

**Nameplate Specifications**

| | | | |
|------------|------------|---------------------|---------------------------------|
| Phase | 3 | Output HP | 5.0 Hp |
| Output KW | 3.7 kW | Voltage | 230/460 V |
| Speed | 1740 r/min | Service Factor | 1.15 |
| Frame | F184T | Enclosure | Totally Enclosed Non Ventilated |
| Efficiency | 87.5 % | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 12.4/6.2 A |
| Duty | Continuous | Insulation Class | B |
| CSA | N | | |

Technical Specifications

| | | | |
|-----------------------|------------|-------------------|------------|
| Poles | 4 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | 206 |
| Opp Drive End Bearing | 204 | Frame Length | 7.20 in |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025