

**Nameplate Specifications**

| | | | |
|------------|------------|---------------------|---------------------------------|
| Phase | 3 | Output HP | 7.50 Hp |
| Output KW | 5.6 kW | Voltage | 230/460 V |
| Speed | 1735 r/min | Service Factor | 1.15 |
| Frame | S213TC | Enclosure | Totally Enclosed Non Ventilated |
| Efficiency | 89.5 % | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 18.6/9.3 A |
| Duty | Continuous | Insulation Class | F |
| UL | Recognized | CSA | Y |

Technical Specifications

| | | | |
|-------------------|----------|-----------------------|-----------------------------|
| Poles | 4 | Rotation | Reversible Counterclockwise |
| Drive End Bearing | 208szz | Opp Drive End Bearing | 206szz |
| Frame Length | 11.00 in | | |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025