

PRODUCT INFORMATION PACKET



Model No: E3030
Catalog No: E3030
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	230/460 V
Speed	3495 r/min	Service Factor	1.15
Frame	215TC	Efficiency	89.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	23/11.5 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	208
Opp Drive End Bearing	207		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025