

PRODUCT INFORMATION PACKET



Model No: E3031
Catalog No: E3031
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	15.0 Hp
Output KW	11.2 kW	Voltage	230/460 V
Speed	3530 r/min	Service Factor	1.15
Frame	254TC	Efficiency	90.2 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	34/17 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	210
Opp Drive End Bearing	208		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025