

PRODUCT INFORMATION PACKET



Model No: E320
Catalog No: E320
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	7.5 Hp
Output KW	5.6 kW	Voltage	230/460 V
Speed	1735 r/min	Service Factor	1.15
Frame	S213T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	89.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	18.6/9.3 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Counterclockwise
Drive End Bearing	208	Opp Drive End Bearing	206
Frame Length	11.00 in		
Connection Drawing	80022802.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025