

**Nameplate Specifications**

Phase	3	Output HP	15.0 Hp
Output KW	11.2 kW	Voltage	230/460 V
Speed	1750 r/min	Service Factor	1.15
Frame	D254TC	Enclosure	Drip Proof
Efficiency	91 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	38.6/19.3 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Counterclockwise
Drive End Bearing	309sf	Opp Drive End Bearing	206sf
Frame Length	12.50 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025