

# PRODUCT INFORMATION PACKET



Model No: E4106  
Catalog No: E4106  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	150.0 Hp
Output KW	111.9 kW	Voltage	460 V
Speed	1785 r/min	Service Factor	1.15
Frame	444TS	Enclosure	Drip Proof
Efficiency	95.8 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	165 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	6318
Opp Drive End Bearing	6318	Frame Length	0.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025