

**Nameplate Specifications**

| | | | |
|------------|------------|---------------------|------------|
| Phase | 3 | Output HP | 300.0 Hp |
| Output KW | 223.8 kW | Voltage | 460 V |
| Speed | 1190 r/min | Service Factor | 1.15 |
| Frame | 449T | Enclosure | Drip Proof |
| Efficiency | 95.4 % | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 354 A |
| Duty | Continuous | Insulation Class | F |
| CSA | Y | | |

Technical Specifications

| | | | |
|-----------------------|------------|-------------------|-----------------------------|
| Poles | 6 | Rotation | Reversible Counterclockwise |
| Mounting | Rigid Base | Drive End Bearing | 6319 |
| Opp Drive End Bearing | 6318 | Frame Length | 19.20 in |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025