

PRODUCT INFORMATION PACKET



Model No: E495
Catalog No: E495
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	25.0 Hp
Output KW	18.7 kW	Voltage	230/460 V
Speed	3530 r/min	Service Factor	1.15
Frame	S256T	Enclosure	Drip Proof
Efficiency	91.7 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	57.0/28.5 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	2	Rotation	Reversible
Drive End Bearing	309sf	Opp Drive End Bearing	207sf
Frame Length	13.00 in		
Connection Drawing	80022802.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025