

PRODUCT INFORMATION PACKET



Model No: E5001
Catalog No: E5001
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	30.0 Hp
Output KW	22.4 kW	Voltage	230/460 V
Speed	3525 r/min	Service Factor	1.15
Frame	S284TS	Enclosure	Drip Proof
Efficiency	91 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	72.0/36.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	2	Rotation	Reversible
Drive End Bearing	213	Opp Drive End Bearing	207
Frame Length	14.00 in		
Connection Drawing	80022801.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025