

# PRODUCT INFORMATION PACKET



Model No: E5003  
Catalog No: E5003  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	25.0 Hp
Output KW	18.7 kW	Voltage	230/460 V
Speed	1740 r/min	Service Factor	1.15
Frame	S284TC	Enclosure	Drip Proof
Efficiency	91.7 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	60.6/30.3 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Counterclockwise
Drive End Bearing	311sf	Opp Drive End Bearing	207sf
Frame Length	14.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025