

**Nameplate Specifications**

Phase	3	Output HP	30.0 22.4KW Hp
Output KW	1663.6 kW	Voltage	200-230/460 V
Speed	3540 r/min	Service Factor	1.15
Frame	S284JP	Enclosure	Drip Proof
Efficiency	89.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	81-70/35 A
Duty	Continuous	Insulation Class	F
CSA	Y		

Technical Specifications

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	313
Opp Drive End Bearing	210	Frame Length	15.08 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025