

# PRODUCT INFORMATION PACKET



Model No: E586  
Catalog No: E586  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	15.0 Hp
Output KW	11.2 kW	Voltage	230/460 V
Speed	1180 r/min	Service Factor	1.15
Frame	284T	Enclosure	Drip Proof
Efficiency	92.4 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	39.2/19.6 A
Duty	Continuous	Insulation Class	F
CSA	Y		

**Technical Specifications**

Poles	6	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	311
Opp Drive End Bearing	210	Frame Length	8.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025