

PRODUCT INFORMATION PACKET



Model No: E607R
Catalog No: E607R
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	50.0 Hp
Output KW	37.3 kW	Voltage	200 V
Speed	1760 r/min	Service Factor	1.15
Frame	D326T	Enclosure	Drip Proof
Efficiency	93 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	141.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible Counterclockwise
Drive End Bearing	312sf	Opp Drive End Bearing	210sf
Frame Length	17.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025