



Nameplate Specifications

Phase	3	Output HP	40.0 Hp
Output KW	29.8 kW	Voltage	200 V
Speed	1780 r/min	Service Factor	1.15
Frame	S324T	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	108 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	312
Opp Drive End Bearing	210		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025