

PRODUCT INFORMATION PACKET



Model No: E731V1
Catalog No: E731V1
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	50 Hp
Output KW	37.3 kW	Voltage	230/460 V
Speed	1190 r/min	Service Factor	1.15
Frame	365T	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	117/58.5 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	6314
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025