



**Nameplate Specifications**

Phase	3	Output HP	75 Hp
Output KW	56.0 kW	Voltage	230/460 V
Speed	1785 r/min	Service Factor	1.15
Frame	365TS	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	174/87 A	Duty	Continuous
Insulation Class	F		

**Technical Specifications**

Rotation	Reversible	Drive End Bearing	6314
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025