



Nameplate Specifications

Phase	3	Output HP	350.0 Hp
Output KW	261.1 kW	Voltage	460 V
Speed	3575 r/min	Service Factor	1.15
Frame	449TS	Efficiency	95.4 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	387 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	314sf
Opp Drive End Bearing	314sf		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025