

PRODUCT INFORMATION PACKET



Model No: K200
Catalog No: K200
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**


Phase	1	Output HP	2.0 Hp
Output KW	1.5 kW	Voltage	115/230 V
Speed	1750 r/min	Service Factor	1
Frame	Y182T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	72.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	24.0/12.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	206
Opp Drive End Bearing	204	Frame Length	8.75 in
Connection Drawing	80022846.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025

A			REV	DATE	ECN	DESCRIPTION	REV BY	APPD
			1	2003/07/23	OOM37030	CONN DIAGRAM NEW SHEET	MLH	JAS



NOTES:

- 1) DRAWING FOR REPRESENTATION ONLY. ACTUAL CONNECTION DIAGRAMS ARE COMPUTER GENERATED AND PRINTED ON ADHESIVE NAMEPLATE 800163.
- 2) RESERVED FOR SINGLE PHASE CONNECTIONS.

800228
ENG. REF.

UNLESS OTHERWISE SPECIFIED		UNLESS OTHERWISE SPECIFIED		DR BY:	MLH	2003/07/23	A.O.SMITH ELECTRICAL PRODUCTS COMPANY		A DIVISION OF A.O.SMITH CORPORATION COPYRIGHT 1995 TIPP CITY, OHIO	
MATERIAL REF.	SURFACE FINISH	.X = ± .X .XX = ± .03 .XXX = ± .010 .XXXX = ± .XXXX ANG = ± 2°		CK BY:	JAS	2003/07/23	TITLE		CONNECTION DIAGRAM	
FRAME	CC	THE INFORMATION HEREON IS THE PROPERTY OF A.O.SMITH AND/OR ITS SUBSIDIARIES. WITHOUT WRITTEN PERMISSION, ANY COPYING, TRANSMITTAL TO OTHERS, AND ANY USE EXCEPT THAT FOR WHICH IT IS LOANED, IS PROHIBITED.		APPD:	JAS	2003/07/23	SIZE	B	DWG NO	80022846
DO NOT SCALE DRAWING		THIRD ANGLE PROJECTION		ISS:		2003/07/23	SCALE	1=4	SHEET 1 OF 1	
AUTOCAD FORM 3										REV 1