

# PRODUCT INFORMATION PACKET



Model No: K300C  
Catalog No: K300C  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





**Nameplate Specifications**

Phase	<b>1</b>	Output HP	<b>5.0 Hp</b>
Output KW	<b>3.7 kW</b>	Voltage	<b>230 V</b>
Speed	<b>1725 r/min</b>	Service Factor	<b>1</b>
Frame	<b>F215TCZ</b>	Enclosure	<b>Totally Enclosed Non Ventilated</b>
Efficiency	<b>78.6 %</b>	Ambient Temperature	<b>40 °C</b>
Frequency	<b>60 Hz</b>	Current	<b>26.0 A</b>
Duty	<b>Continuous</b>	Insulation Class	<b>B</b>
UL	<b>Recognized</b>	CSA	<b>Y</b>

**Technical Specifications**

Poles	<b>4</b>	Rotation	<b>Reversible</b>
Mounting	<b>Rigid Base</b>	Drive End Bearing	<b>310</b>
Opp Drive End Bearing	<b>206</b>	Frame Length	<b>9.00 in</b>

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025