

PRODUCT INFORMATION PACKET



Model No: 93285-31
Catalog No: 93285-31
B-93285-31 TACHOMTR/ HSD381024843A2C

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/04/2025

DYNAPAR HSD38

HSD38

B

B

B

B

C

D

E

F

G

H

CODE 7: OPTIONS				H
CAST ALUMINUM HOUSING, SLOTTED TETHER INCLUDED				0
CAST ALUMINUM HOUSING, NO TETHER				6
CAST ALUMINUM HOUSING, SINGLE-POINT TETHER INCLUDED (NEMA 4.5 C-FACE)				C
SAME AS "0" WITH COVER KIT				D
SAME AS "C" WITH COVER KIT				E
CAST ALUMINUM HOUSING, SINGLE-POINT TETHER INCLUDED (NEMA 8-1/2" C-FACE)				K
SAME AS "K" WITH COVER KIT				N
CODE 7: OPTIONS				G
NO OPTION				0
INTERNALLY ISOLATED 1" BORE				1
CODE 6: TERMINATION				F
6 PIN CONNECTOR				0
7 PIN CONNECTOR				1
10 PIN CONNECTOR				2
10 PIN BAYONET CONNECTOR				4
6 PIN CONNECTOR, PLUS MATING CONNECTOR				5
7 PIN CONNECTOR, PLUS MATING CONNECTOR				6
10 PIN CONNECTOR, PLUS MATING CONNECTOR				7
10 PIN BAYONET CONNECTOR PLUS MATING CONNECTOR				8
18" (.5m) CABLE				A
36" (1m) CABLE				B
72" (2m) CABLE				C
13' (.3m) CONNECTOR				G
8 PIN M12 CONNECTOR				J
18" (.5m) CABLE WITH 10 PIN IN-LINE CONNECTOR				K
AVAILABLE WHEN CODE 5 IS 0 OR 2:				
5 PIN M12 CONNECTOR				H
CODE 5: OUTPUT				F
5-26V IN, 5-26V OPEN COLLECTOR OUT (7273)				0
5-26V IN, 5-26V PUSH-PULL OUT				2
AVAILABLE WHEN CODE 4 IS 3 OR 4:				
5-26V IN, 5-26V DIFFERENTIAL LINE DRIVER OUT (7272)				2
5-26V IN, 5V DIFFERENTIAL LINE DRIVER OUT (7272)				2
CODE 4: FORMAT				D
SINGLE ENDED, UNIDIRECTIONAL (A)				0
SINGLE ENDED BIDIRECTIONAL (AB)				1
SINGLE ENDED BIDIRECTIONAL WITH INDEX (ABZ)				2
AVAILABLE WHEN CODE 5 IS 3 OR 4 AND CODE 6 IS 1, 2, 4, 6, 7, 8, A, G, J, OR K:				
DIFFERENTIAL, BIDIRECTIONAL (AA BB)				3
AVAILABLE WHEN CODE 5 IS 3 OR 4 AND CODE 6 IS 2, 4, 6, 7, A, G, J, OR K:				
DIFFERENTIAL, BIDIRECTIONAL WITH INDEX (AA BB ZZ)				4
CODE 3: BORE SIZE				C
6 12mm	9 15mm	7 1/2"	8 5/8"	NOT ELECTRICALLY ISOLATED
A 16mm	C 3/4"	D 20mm	E 7/8"	G 1"
CODE 2: PPR				B
0015, 0032, 0050, 0060, 0100, 0200, 0240, 0250, 0500, 0512, 0600, 1000, 1024, 1200, 2000, 2048, 4000, 4096, 5000				

