

PRODUCT INFORMATION PACKET



Model No: E630V1
Catalog No: E630V1
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	50.0 Hp
Output KW	37.3 kW	Voltage	230/460 V
Speed	1775 r/min	Service Factor	1.15
Frame	326T	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	115/57.5 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	313
Opp Drive End Bearing	311		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025