

**Nameplate Specifications**

Phase	3	Output HP	50 Hp
Output KW	37.3 kW	Voltage	230/460 V
Speed	3555 r/min	Service Factor	1.15
Frame	324TS	Efficiency	93 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	118/59 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	6312
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025