

**Nameplate Specifications**

Phase	3	Output HP	75 Hp
Output KW	56.0 kW	Voltage	230/460 V
Speed	1785 r/min	Service Factor	1.15
Frame	365T	Enclosure	Drip Proof
Efficiency	95 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	174/87 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	314s
Opp Drive End Bearing	312s	Frame Length	0.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025