

# PRODUCT INFORMATION PACKET



Model No: E729V1  
Catalog No: E729V1  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





**Nameplate Specifications**

Phase	<b>3</b>	Output HP	<b>100 Hp</b>
Output KW	<b>74.6 kW</b>	Voltage	<b>460 V</b>
Speed	<b>3565 r/min</b>	Service Factor	<b>1.15</b>
Frame	<b>365TS</b>	Efficiency	<b>93.6 %</b>
Ambient Temperature	<b>40 °C</b>	Frequency	<b>60 Hz</b>
Current	<b>110 A</b>	Duty	<b>Continuous</b>
Insulation Class	<b>F</b>		

**Technical Specifications**

Rotation	<b>Reversible</b>	Drive End Bearing	<b>6312</b>
Opp Drive End Bearing	<b>6312</b>		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025