

**Nameplate Specifications**

Phase	3	Output HP	75.0 Hp
Output KW	56.0 kW	Voltage	200 V
Speed	1785 r/min	Service Factor	1.15
Frame	Y365T	Efficiency	95 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	200 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	314
Opp Drive End Bearing	212		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025