

PRODUCT INFORMATION PACKET



Model No: E757
Catalog No: E757
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	150 Hp
Output KW	111.9 kW	Voltage	460 V
Speed	3580 r/min	Service Factor	1.15
Frame	405TS	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	162 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	6313
Opp Drive End Bearing	6313		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025