

**Nameplate Specifications**

Phase	3	Output HP	50 Hp
Output KW	37.3 kW	Voltage	575 V
Speed	1780 r/min	Service Factor	1.15
Frame	326T	Efficiency	94.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	47 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	6312
Opp Drive End Bearing	6312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025