

# PRODUCT INFORMATION PACKET



Model No: K221  
Catalog No: K221  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	1	Output HP	7.0-10.5 Hp
Output KW	5.2 kW	Voltage	200-230 V
Speed	3450 r/min	Service Factor	1
Frame	D184TZ	Enclosure	Open Drip Proof
Efficiency	82 %	Ambient Temperature	50 °C
Frequency	60 Hz	Current	48.0-41.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	2	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	206
Opp Drive End Bearing	206	Frame Length	8.33 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025