

**Nameplate Specifications**

| | | | |
|------------|------------|---------------------|---------------------------------|
| Phase | 1 | Output HP | 3.0 Hp |
| Output KW | 2.2 kW | Voltage | 115/230 V |
| Speed | 3500 r/min | Service Factor | 1 |
| Frame | H184T | Enclosure | Totally Enclosed Non Ventilated |
| Efficiency | 75.5 % | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 30/15 A |
| Duty | Continuous | Insulation Class | B |
| UL | Recognized | CSA | Y |

Technical Specifications

| | | | |
|-----------------------|------------|-------------------|------------|
| Poles | 2 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | 206 |
| Opp Drive End Bearing | 204 | Frame Length | 9.75 in |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025