

**Nameplate Specifications**

Phase	3	Output HP	1.5 Hp
Output KW	1.1 kW	Voltage	230/460 V
Speed	1730 r/min	Service Factor	1.15
Frame	145T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	86.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	4.2/2.1 A	Duty	Continuous
Insulation Class	F	Number of Speeds	1

**Technical Specifications**

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	6205zz
Opp Drive End Bearing	6205zz		
Connection Drawing	80022802		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/04/2025