

**Nameplate Specifications**

Phase	3	Output HP	350.0 Hp
Output KW	261.1 kW	Voltage	460 V
Speed	1785 r/min	Service Factor	1.15
Frame	449T	Enclosure	Drip Proof
Efficiency	95.4 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	387 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	322
Opp Drive End Bearing	314	Frame Length	19.20 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025