

**Nameplate Specifications**

Phase	3	Output HP	7.5 Hp
Output KW	5.6 kW	Voltage	230/460 V
Speed	1170 r/min	Service Factor	1.15
Frame	S254T	Enclosure	Drip Proof
Efficiency	88.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	22.6/11.3 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	6	Rotation	Counterclockwise
Drive End Bearing	309	Opp Drive End Bearing	207
Frame Length	13.00 in		
Connection Drawing	80022802.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025