

# PRODUCT INFORMATION PACKET



Model No: E454V1  
Catalog No: E454V1  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	15 Hp
Output KW	11.2 kW	Voltage	200 V
Speed	1750 r/min	Service Factor	1.15
Frame	S254T	Enclosure	Drip Proof
Efficiency	91 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	42.2 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Counterclockwise
Drive End Bearing	309	Opp Drive End Bearing	207
Frame Length	13.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025