

PRODUCT INFORMATION PACKET



Model No: E462V1
Catalog No: E462V1
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	15.0 Hp
Output KW	11.2 kW	Voltage	575 V
Speed	1765 r/min	Service Factor	1.15
Frame	254T	Efficiency	92.4 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	15.2 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	210
Opp Drive End Bearing	208		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025