



Nameplate Specifications

Phase	3	Output HP	20.0 Hp
Output KW	14.9 kW	Voltage	575 V
Speed	1765 r/min	Service Factor	1.15
Frame	256T	Efficiency	93 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	19.5 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	210
Opp Drive End Bearing	208		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025