

PRODUCT INFORMATION PACKET



Model No: E487
Catalog No: E487
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	20.0 Hp
Output KW	14.9 kW	Voltage	230/460 V
Speed	3505 r/min	Service Factor	1.15
Frame	S254TCZ	Enclosure	Drip Proof
Ambient Temperature	40 °C	Frequency	60 Hz
Current	51.0/25.5 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y		

Technical Specifications

Poles	2	Rotation	Reversible
Drive End Bearing	309sf	Opp Drive End Bearing	207sf
Frame Length	13.00 in		
Connection Drawing	80022801.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025