



Nameplate Specifications

Phase	3	Output HP	30.0 Hp
Output KW	22.4 kW	Voltage	200 V
Speed	1760 r/min	Service Factor	1.15
Frame	S286T	Enclosure	Drip Proof
Efficiency	92.4 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	86.5 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Counterclockwise
Drive End Bearing	311	Opp Drive End Bearing	207
Frame Length	14.00 in		
Connection Drawing	80022803.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025