

PRODUCT INFORMATION PACKET



Model No: E551V1
Catalog No: E551V1
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	25.0 Hp
Output KW	18.7 kW	Voltage	575 V
Speed	1775 r/min	Service Factor	1.15
Frame	284T	Efficiency	93.6 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	24.6 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	311
Opp Drive End Bearing	309		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025