

**Nameplate Specifications**

Phase	3	Output HP	40.0 Hp
Output KW	29.8 kW	Voltage	230/460 V
Speed	3540 r/min	Service Factor	1.15
Frame	S286TS	Enclosure	Drip Proof
Efficiency	92.4 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	90.0/45.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	2	Rotation	Reversible
Drive End Bearing	213sf	Opp Drive End Bearing	207sf
Frame Length	14.00 in		
Connection Drawing	80022801.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025