

# PRODUCT INFORMATION PACKET



Model No: E601R  
Catalog No: E601R  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	50.0 Hp
Output KW	37.3 kW	Voltage	230/460 V
Speed	1760 r/min	Service Factor	1.15
Frame	D326T	Enclosure	Drip Proof
Efficiency	93 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	122.0/61.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Reversible Counterclockwise
Drive End Bearing	312sf	Opp Drive End Bearing	210sf
Frame Length	17.00 in		
Connection Drawing	80022801.PCX		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025