

PRODUCT INFORMATION PACKET



Model No: E723
Catalog No: E723
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	75.0 Hp
Output KW	56.0 kW	Voltage	575 V
Speed	1780 r/min	Service Factor	1.15
Frame	365T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	95.4 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	69.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	314sf
Opp Drive End Bearing	212sf	Frame Length	14.30 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025