

**Nameplate Specifications**

Phase	3	Output HP	100 Hp
Output KW	74.6 kW	Voltage	200 V
Speed	1780 r/min	Service Factor	1.15
Frame	404T	Efficiency	94.1 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	257.0 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible	Drive End Bearing	317
Opp Drive End Bearing	312		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025