

PRODUCT INFORMATION PACKET



Model No: E927
Catalog No: E927
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	15.0 Hp
Output KW	11.2 kW	Voltage	575 V
Speed	1770 r/min	Service Factor	1.15
Frame	S254T	Enclosure	Drip Proof
Efficiency	93 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	15.1 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y

Technical Specifications

Poles	4	Rotation	Counterclockwise
Drive End Bearing	309sf	Opp Drive End Bearing	207sf
Frame Length	13.00 in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025