



Nameplate Specifications

Phase	3	Output HP	100 Hp
Output KW	74.6 kW	Voltage	575 V
Speed	1785 r/min	Service Factor	1.15
Frame	404T	Efficiency	95.4 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	95 A	Duty	Continuous
Insulation Class	F		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	6317
Opp Drive End Bearing	6313		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025