

**Nameplate Specifications**

Phase	1	Output HP	7.5 Hp
Output KW	5.6 kW	Voltage	230 V
Speed	1745 r/min	Service Factor	1
Frame	F215T	Enclosure	Totally Enclosed Non Ventilated
Efficiency	84 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	34.0 A
Duty	Continuous	Insulation Class	B
UL	Recognized	CSA	Y

**Technical Specifications**

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	307
Opp Drive End Bearing	206	Frame Length	9.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025