

PRODUCT INFORMATION PACKET



Model No: E372
Catalog No: E372
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Phase	3	Output HP	10.0 Hp
Output KW	7.5 kW	Voltage	230/460 V
Speed	3450 r/min	Service Factor	1.15
Frame	S213JP	Efficiency	85.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	24.4/12.2 A	Duty	Continuous
Insulation Class	B		

Technical Specifications

Rotation	Reversible Counterclockwise	Drive End Bearing	310
Opp Drive End Bearing	206		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025