

**Nameplate Specifications**

Phase	3	Output HP	15.0 Hp
Output KW	11.2 kW	Voltage	230/460 V
Speed	1755 r/min	Service Factor	1.15
Frame	254TC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Frequency	60 Hz	Current	36.0/18.0 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	Y
Number of Speeds	1		

Technical Specifications

Rotation	Reversible	Mounting	Rigid Base
Drive End Bearing	Ball	Opp Drive End Bearing	Ball

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025