

**Nameplate Specifications**

Phase	3	Output HP	200.0 Hp
Output KW	149.2 kW	Voltage	460 V
Speed	1785 r/min	Service Factor	1.15
Frame	445T	Enclosure	Drip Proof
Efficiency	95.8 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	218 A
Duty	Continuous	Insulation Class	F
UL	Recognized	CSA	N

**Technical Specifications**

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	6318
Opp Drive End Bearing	6318	Frame Length	0.00 in

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025