

# PRODUCT INFORMATION PACKET



Model No: E415  
Catalog No: E415  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





**Nameplate Specifications**

Phase	<b>3</b>	Output HP	<b>10.0 Hp</b>
Output KW	<b>7.5 kW</b>	Voltage	<b>230/460 V</b>
Speed	<b>1170 r/min</b>	Service Factor	<b>1.15</b>
Frame	<b>S256T</b>	Enclosure	<b>Drip Proof</b>
Efficiency	<b>90.2 %</b>	Ambient Temperature	<b>40 °C</b>
Frequency	<b>60 Hz</b>	Current	<b>28.4/14.2 A</b>
Duty	<b>Continuous</b>	Insulation Class	<b>F</b>
UL	<b>Recognized</b>	CSA	<b>Y</b>

**Technical Specifications**

Poles	<b>6</b>	Rotation	<b>Counterclockwise</b>
Drive End Bearing	<b>309sf</b>	Opp Drive End Bearing	<b>207sf</b>
Frame Length	<b>13.00 in</b>		
Connection Drawing	<b>80022801.PCX</b>		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025